## **SmartButton**

## **Product Specifications**

**GENERAL SPECIFICATIONS** 

**Size:** 17 mm diameter x 6 mm height (0.67" x 0.24")

Weight: 4 grams (0.14 ounces)

Case Material:Stainless steelBattery:3.0 volt LithiumResolution:8-bit (1 part in 256)

**Mounting:** User selectable (magnetic backing, plastic plate mount, or

angled blue hard plastic)

Clock Accuracy: +/- 2 minutes per month from 0 to 45°C (32 to 113°F)

Sampling Methods: Continuous (First-in, First-out), Stop When Full (Fill-then-stop)

**Operating Limits:**  $-40^{\circ}\text{C}$  to  $85^{\circ}\text{C}$  ( $-40^{\circ}\text{F}$  to  $185^{\circ}\text{F}$ )

PC Requirements: Pentium® 75 (Pentium® II or faster recommended) running

Windows® 9X/NT/2000/XP with at least 16MB RAM (64MB RAM strongly recommended), color monitor, 16-bit color graphics card, printer, pointing devices and one free serial port

Software Requirements: SmartButton Reader

**Communication:** RS232 Serial/ACR SmartButton interface

Memory Size: 2KB (capable of storing up to 2,048 readings)
Sampling Rates: User selectable rates from 1 minute to 255 minutes

Start Delay: Up to 255 minutes

**Number of Channels:** One (one internal channel for ambient temperature)

Alarm Thresholds User selectable, event storage

## **SENSOR SPECIFICATIONS**

**Temperature Sensor:** 

Type: Silicon

Range: -40 to 85°C (-40 to 185°F)

Accuracy: +/- 1.0°C from -30 to 45°C (+/- 1.8°F from -22 to 113°F)

+/- 1.5°C from 45.5 to 85°C (+/- 2.7°F from 114 to 185°F)

The ACR SmartButton is a miniature-sized temperature logger that is extremely low-cost and easy to use. Because of its small size and low-cost, you can purchase tens or hundreds of them for multiple-site temperature monitoring. To get you started, purchase the SmartButton Starter Pack. It includes one SmartButton, an interface cable, the SmartButton Reader software, and a mini manual. So simple and easy to use, anyone can start data logging today!



Type: Single-Channel Temperature

WARRANTY
Data Logger:

1 Year

## **APPLICATIONS**

Food processing verification, pharmaceutical storage, laboratories, transportation of temperature-sensitive goods, equipment run time, HVAC system testing and balancing, etc.

Model#: Cat#:

SmartButton (single) 01-0180 SmartButton Starter Pack 01-0181

> Page 1 of 1 Rev: 8-11/03/05