

Van Guard®

1200-Series Clinical Microscopes

VanGuard 1200-Series Clinical Microscopes provide the necessary specifications for diagnostic & educational use in medical/veterinary clinics, universities, and industrial laboratories.

Wide ranges of models are available in Brightfield & Phase Contrast configurations. Choose from standard achromatic or plan achromatic objectives; monocular, binocular, or trinocular viewing heads.

Various camera packages are available as options; including digital, video, and 35mm systems.

All models feature 10X WideField eyepieces, 20W variable quartz halogen, field diaphragms for Koehler illumination, and are backed by a 5-Year warranty.

Make your lab work better...make it VanGuard.

Technical Specifications

| recilling | ai Specifica | 1110115 | | | | | | | | | | | |
|---------------------------|------------------------------------|------------------------------------------------|------------------------------------|------------------------------------------------|------------------------------------|--------------------------------------|-------------------------------------------------|------------------------------|------------------------------------------|-------------------------------------------------|------------------------------|--------------------|-------------|
| | | 1210CM | 1220CM | 1230CM | 1211CM | 1221CM | 1231CM | 1212CM | 1222CM | 1232CM | 1213CM | 1223CM | 1233CM |
| Optical System | | Fixed 160mm | | Fixed 160mm | | Fixed 160mm | | Fixed 160mm | | | | | |
| | Туре | Monocular | Binocular | Trinocular | Monocular | Binocular | Trinocular | Monocular | Binocular | Trinocular | Monocular | Binocular | Trinocular |
| | Tube Inclinination | 30° | | 30° | | 30° | | 30° | | | | | |
| Viewing Head | Rotatable | 360° | | 360° | | 360° | | 360° | | | | | |
| • | Interpupillary | N/A 55-75mm | | N/A | 55-75mm | | N/A | 55-75mm | | N/A 55-75mm | | | |
| | Dioptric | N/A | -5 to +5 | | N/A | -5 to +5 | | N/A | -5 to +5 | | N/A -5 to + | | 0 +5 |
| Camera Port | - | N/A | N/A | 20/80 Split | N/A | N/A | 20/80 Split | N/A | N/A | 20/80 Split | N/A | N/A | 20/80 Split |
| | Magnification | 10X | | 10X | | 10X | | | 10X | | | | |
| | Туре | WideField | | WideField | | | WideField | | | WideField | | | |
| Eyepieces | Field Diameter | 18mm | | 18mm | | | 18mm | | | 18mm | | | |
| | HIgh-Eyepoint | Yes | | Yes | | | Yes | | | Yes | | | |
| | Rubber Eyecups | Yes | | | Yes | | | Yes | | | Yes | | |
| Nosepiece Positions | | 4 | | | 4 | | | 4 | | | 4 | | |
| | Pitch | Reverse | | | Reverse | | | Reverse | | | Reverse | | |
| Illumination Technique(s) | | Brightfield | | | Brightfield | | | Brightfield / Phase Contrast | | | Brightfield / Phase Contrast | | |
| Objectives | Туре | Achromatic | | Plan Achromatic | | | Achromatic | | | Plan Achromatic | | | |
| | Magnification (N.A.) | 4X (0.10), 10X (0.25), 40X (0.60), 100X (1.25) | | 4X (0.10), 10X (0.25), 40X (0.60), 100X (1.25) | | | 10X (0.25), 20X (0.40), 40X (0.60), 100X (1.25) | | | 10X (0.25), 20X (0.40), 40X (0.60), 100X (1.25) | | | |
| | DIN Standard | Yes | | | Yes | | | Yes | | | Yes | | |
| | Туре | Mechanical | | Mechanical | | | Mechanical | | | Mechanical | | | |
| | Shape | Rectangular | | Rectangular | | | Rectangular | | | Rectangular | | | |
| Stage | Dimensions | 160 x 140mm | | 160 x 140mm | | 160 x 140mm | | | 160 x 140mm | | | | |
| | X-Y Control | Drop-Down, Right-Hand, Rack & Pinion | | Drop-Down, Right-Hand, Rack & Pinion | | Drop-Down, Right-Hand, Rack & Pinion | | | Drop-Down, Right-Hand, Rack & Pinion | | | | |
| | Cross Travel Range | 75 x 50mm | | 75 x 50mm | | 75 x 50mm | | | 75 x 50mm | | | | |
| | Slide Holder | Removable Spring Clip | | Removable Spring Clip | | Removable Spring Clip | | | Removable Spring Clip | | | | |
| | Finish | Chemical Resistant | | Chemical Resistant | | Chemical Resistant | | | Chemical Resistant | | | | |
| Focusing | Туре | Coaxial | | Coaxial | | Coaxial | | | Coaxial | | | | |
| | Controls | Coarse/ Fine | | Coarse/ Fine | | | Coarse/ Fine | | | Coarse/ Fine | | | |
| | Tension Adjustment | Yes | | Yes | | | Yes | | | Yes | | | |
| | Safety Auto-Stop | Yes | | Yes | | | Yes | | | Yes | | | |
| | Focusing Range | 40mm | | 40mm | | 40mm | | | 40mm | | | | |
| | Precision | 0.002mm | | 0.002mm | | 0.002mm | | | 0.002mm | | | | |
| Condenser | Туре | Abbe 1.25 N.A. w/ Iris Diaphragm | | Abbe 1.25 N.A. w/ Iris Diaphragm | | Abbe 1.25 N.A. w/ Iris Diaphragm | | | Abbe 1.25 N.A. w/ Iris Diaphragm | | | | |
| | Focusing Control | Rack & Pinion | | Rack & Pinion | | Rack & Pinion | | | Rack & Pinion | | | | |
| | Zernike Phase Annuli | N/A | | N/A | | 10X, 20X, 40X, & 100X | | | 10X, 20X, 40X, & 100X | | | | |
| Illumination | Туре | 20W Variable Quartz Halogen | | 20W Variable Quartz Halogen | | 20W Variable Quartz Halogen | | | 20W Variable Quartz Halogen | | | | |
| | Koehler | Field Diaphragm | | Field Diaphragm | | Field Diaphragm | | | Field Diaphragm | | | | |
| | Filter Holder | On Collector | | On Collector | | On Collector | | | On Collector | | | | |
| Base | 210 x 180mm; Anti-Skid Rubber Feet | | 210 x 180mm; Anti-Skid Rubber Feet | | 210 x 180mm; Anti-Skid Rubber Feet | | 210 x 180mm; Anti-Skid Rubber Feet | | | | | | |
| Body | Ergonomic; Stain-Resistant Enamel | | | | Stain-Resistant Enamel Finish | | Ergonomic; Stain-Resistant Enamel Finish | | Ergonomic; Stain-Resistant Enamel Finish | | | | |
| Dimensions | | 210 (L) x 180 (W) x 380 (H) mm | | 210 (L) x 180 (W) x 380 (H) mm | | 210 (L) x 180 (W) x 380 (H) mm | | | 210 (L) x 180 (W) x 380 (H) mm | | | | |
| Weight | | 7.0kg | | 7.0kg | | 7.0kg | | | 7.0kg | | | | |
| Voltage | 110V (220V Available On Re | | <u> </u> | | V Available On Request) | | 110V (220V Available On Request) | | | 110V (220V Available On Request) | | | |
| Warranty | | 5-Year Optica | I/Mechanical; 1- | Year Electrical | 5-Year Optical | I/Mechanical; 1- | Year Electrical | | I/Mechanical; 1- | | | /Mechanical; 1- | |
| | | Clear Diffusing | Filter. Blue Filter | Spare Lamps & | Clear Diffusing F | Filter, Blue Filter. | Spare Lamps & | _ | Filter, Blue Filt | | | Filter, Blue Filte | |
| Supplied With | | | t Cover, & Opera | | | Cover, & Operat | | | repiece, Spare L | | | epiece, Spare L | |
| | | , | , , | | | , | | Dust Co | ver, & Operation | Manual | Dust Co | ver, & Operation | Manual |

Printed in the IISA

No. PS022009PSMS1200CMSRRI-A